

HA CUT™ Cat F/XF/SXF AF

Next generation, phthalate free Fast, eXtra-Fast and Super eXtra-Fast catalysts for use with HA Cut AF and HA Cut CFL AF closed cell 1-component polyurethane injection resins

Product Description

HA CUT™ Cat F/XF/SXF AF are red non-flammable, phthalate free liquids. HA Cut Cat F/XF/SXF AF are catalysts for HA Cut AF and HA Cut CFL AF water cutting resin for applications in cold temperatures or when use of the standard catalyst does not give a fast enough reaction. HA Cut Cat F/XF/SXF AF are used in 10% mixing ratio.

Application

Before commencing the injection, consult the consult the Technical Data Sheets and Material Safety Data Sheet (MSDS) in order to be familiar with the materials at hand. Always shake the catalyst well before use.

1. Resin and equipment preparation

- Prepare the resin with the predetermined amount of catalyst. Shake HA Cut Cat F/XF/SXF AF well before use. No reaction with the resin will occur until the resin comes into contact with water.
- Keep the resin protected from water, since this will trigger a reaction in the container used and might cause the resin to harden or foam prematurely within the injection equipment.
- Due to the high reactivity of Ha Cut Cat F/XF/SXF AF, it is highly recommended to remove filters from the pumps and maintain full pump reservoirs when working with Ha Cut Cat F/XF/SXF AF to prevent blockage of the pump.
- It is highly recommended to use separate pumps for the water and the resin injection to prevent cross contamination and blockages.

Field of Application

- HA Cut AF / HA Cut CFL AF catalyst for cutting off gushing leaks with a high to very high flow rate and/or high to very high pressure, where use of the standard catalyst does not result in a fast enough reaction.
- HA Cut AF / HA Cut CFL AF catalyst for use in cold to very cold temperatures where fast reaction times are needed.

Product Advantages

- ADR free transport.
- Next generation phthalate free catalysts, REACH compliant. Improved performance at temperatures below 5 ° C, no crystallisation of HA Cut Cat F/XF/SXF AF.
- Non-flammable, solvent free.
- Final foam is resistant to most organic solvents, mild acids, alkaloids and microorganisms.
- Very fast reaction: as fast as less than 60" in salt water at -3°C, still giving 20V expansion (HA Cut Cat SXF AF) (*).
 (*) For chemical resistances please contact your local GCP representative.



2. Injection

• Please refer to the HA Cut AF / HA Cut CFL AF Technical Data Sheet for further information.

3. Reactivity

Reactivity for HA Cut AF

	START REACTION	END REACTION	EXPANSION
10% HA Cut Cat F AF			
-3°C	Approx. 30"	Approx. 1'40"	Approx. 20V
5°C	Approx. 28"	Approx. 1'25"	Approx. 26V
10°C	Approx. 26"	Approx. 1'23"	Approx. 26V
15°C	Approx. 23"	Approx. 1'20"	Approx. 28V
20°C	Approx. 23"	Approx. 1'20"	Approx. 30V
25°C	Approx. 20"	Approx. 1'20"	Approx. 32V
10% HA Cut Cat XF AF			
-3°C	Approx. 25"	Approx. 1'15"	Approx. 24V
5°C	Approx. 23"	Approx. 1'10"	Approx. 28V
10°C	Approx. 23"	Approx. 1'10"	Approx. 28V
15°C	Approx. 23"	Approx. 1'05"	Approx. 30V
20°C	Approx. 20"	Approx. 1'05"	Approx. 30V
25°C	Approx. 18"	Approx. 1'05"	Approx. 32V
10% HA Cut Cat SXF AF			
-3°C	Approx. 22"	Approx. 1'05"	Approx. 30V
5°C	Approx. 20"	Approx. 1'00"	Approx. 30V
10°C	Approx. 20"	Approx. 1'00"	Approx. 30V
15°C	Approx. 20"	Approx. 55"	Approx. 32V
20°C	Approx. 20"	Approx. 50"	Approx. 32V
25°C	Approx. 15"	Approx. 45"	Approx. 35V

Reactivity for HA Cut CFL AF

	START REACTION	END REACTION	EXPANSION
10% HA Cut Cat F AF			
-3°C	Approx. 28"	Approx. 2'00"	Approx. 24V
5°C	Approx. 25"	Approx. 1'40"	Approx. 26V



10°C	Approx. 25"	Approx. 1'35"	Approx. 26V	
15°C	Approx. 25"	Approx. 1'30"	Approx. 28V	
20°C	Approx. 25"	Approx. 1'20"	Approx. 28V	
25°C	Approx. 20"	Approx. 1'15"	Approx. 30V	
10% HA Cut Cat XF AF				
-3°C	Approx. 25"	Approx. 1'30"	Approx. 24V	
5°C	Approx. 20"	Approx. 1'10"	Approx. 26V	
10°C	Approx. 20"	Approx. 1'10"	Approx. 26V	
15°C	Approx. 20"	Approx. 1'05"	Approx. 28V	
20°C	Approx. 20"	Approx. 1'00"	Approx. 30V	
25°C	Approx. 15"	Approx. 1'00"	Approx. 30V	
10% HA Cut Cat SXF AF				
-3°C	Approx. 20"	Approx. 1'00"	Approx. 28V	
5°C	Approx. 18"	Approx. 55″	Approx. 30V	
10°C	Approx. 18"	Approx. 55″	Approx. 30V	
15°C	Approx. 17"	Approx. 55″	Approx. 30V	
20°C	Approx. 15"	Approx. 45″	Approx. 30V	
25°C	Approx. 10"	Approx. 40"	Approx. 30V	

Technical Data/Properties

	VALUE		NORM
HA Cut Cat F AF	HA Cut Cat XF AF	HA Cut Cat SXF AF	
Approx. 20	Approx. 20	Approx. 25	EN ISO 3251
Approx. 0.973	Approx. 1.000	Approx. 1.044	EN ISO 2811
125	125	125	EN ISO 2719
Approx. 1.000	Approx. 1.000	Approx. 1.000	EN ISO 1183
	>23		EN 12190
Approx. 1.000	Approx. 1.000	Approx. 1.000	EN ISO 1183
	>5		EN 12190
	>7		EN 12190
	Approx. 20 Approx. 0.973 125 Approx. 1.000	HA Cut Cat F AF Approx. 20 Approx. 0.973 Approx. 1.000 125 Approx. 1.000 Approx. 1.000 >23 Approx. 1.000 Approx. 1.000 >5	HA Cut Cat F AF HA Cut Cat XF AF HA Cut Cat SXF AF Approx. 20 Approx. 20 Approx. 25 Approx. 0.973 Approx. 1.000 Approx. 1.044 125 125 Approx. 1.000 Approx. 1.000 Approx. 1.000 >23 Approx. 1.000 Approx. 1.000 Approx. 1.000 >5



Appearance

HA Cut Cat F/XF/SXF AF: Red liquids.

Consumption

HA Cut Cat F/XF/SXF AF are developed solely for cutting of high flow gushing leaks where very fast reaction times are needed.

The consumption is always 10% of the Ha Cut AF / HA Cut CFL AF volume for HA Cut Cat F/XF/SXF AF.

Packaging

HA Cut Cat F/XF/SXF AF

0.5 or 2.5L plastic bottle or 20kg metal drum.

1 box	8 x 2.5L	
1 box	5 x 2.5L	
1 Pallet	40 boxes with 2.5L bottles	
	24 x 20kg metal drums	

Storage

HA Cut Cat F/XF/SXF AF are sensitive to moisture and should be stored in original containers in a dry area. Storage temperature must be between 5 °C and 30 °C. Once the packaging has been opened, the useful life of the material is greatly reduced and should be used as soon as possible.

Shelf life: 2 years.

Health and Safety

HA Cut AF is classified as harmful.

HA Cut CFL AF is classified as harmful.

HA Cut Cat F/XF/SXF AF is classified as irritant.

In case of spills and accidents, refer to the MSDS of the products or when in doubt contact your local GCP representative.

Always wear protective clothing, gloves and protective goggles when handling chemical products.

For full information, consult the relevant MSDS.



gcpat.hk | For technical information: asia.enq@gcpat.com

We hope the information here will be helpful. It is based on data and knowledge considered to be true and accurate, and is offered for consideration, investigation and verification by the user, but we do not warrant the results to be obtained. Please read all statements, recommendations, and suggestions in conjunction with our conditions of sale, which apply to all goods supplied by us. No statement, recommendation, or suggestion is intended for any use that would infringe any patent, copyright, or other third party right.

Cut and HA are trademarks, which may be registered in the United States and/or other countries, of GCP Applied Technologies, Inc. This trademark list has been compiled using available published information as of the publication date and may not accurately reflect current trademark ownership or status.

© Copyright 2017 GCP Applied Technologies, Inc. All rights reserved.

GCP Applied Technologies Inc., 2325 Lakeview Parkway, Alpharetta, GA 30009, USA

GCP (Hong Kong) Ltd., 6 On Chuen Street, On Lok Tsuen Ind Area, Fanling, Hong Kong

This document is only current as of the last updated date stated below and is valid only for use in Hong Kong. It is important that you always refer to the currently available information at the URL below to provide the most current product information at the time of use. Additional literature such as Contractor Manuals, Technical Bulletins, Detail Drawings and detailing recommendations and other relevant documents are also available on www.gcpat.hk. Information found on other websites must not be relied upon, as they may not be up-to-date or applicable to the conditions in your location and we do not accept any responsibility for their content. If there are any conflicts or if you need more information, please contact GCP Customer Service.

Last Updated: 2023-07-07